

## VALOR™ LOCKER ORDERING GUIDE

**Step 1 - Determine the width needed for your locker requirements.** Lockers are offered in 18" or 24" wide.

**Step 2 - Select upper shell configuration**  
**Configuration A** - A partition kit comprised of; two utility hooks, a coat rod, a partition and full width shelf. This option will support all personal compartment options.

**Configuration B** - Choose full width shelves and/or stand alone security compartments to fill this locker requirement.

**Step 3 - Determine if a Lower Unit Boot Drawer is required.** A boot drawer is equipped to provide storage for larger gear and has a hardwood bench top\* that provides a seating option when changing. A vest shelf may also be added to the lower drawer unit.

**Step 4 - Select Additional Locker Door Options**  
 • belt clips • clip board holder • magnetic mirror

\*For multiple locker runs, Lyon recommends purchasing by linear foot. For a quote, contact customer service.

### Step 1

#### 18" Locker Units and Options

Size	Description	Cat. No.
18"w x 24"d x 72"h	Upper Unit Shell	<b>VL5104</b>

#### 24" Locker Units and Options

Size	Description	Cat. No.
24"w x 24"d x 72"h	Upper Unit Shell	<b>VL5578</b>

### Step 2 Configuration A

Upper Unit Partition Kit consists of the following components (to configure locker using partition kit see personal compartment options below)		
18"w x 24"d	Partition Kit	<b>VL1858PT</b>
18"w	Full Width Shelf†	
-	Two Utility Hooks	
18"w	Coat Rod	
Upper Unit options AVAILABLE ONLY WITH a Partition Kit		
Personal Compartment Options		
8"w x 8"h	Security Compartment Door Kit**	<b>VL0808LU</b>
8"w x 8"h	Two Drawer/Shelf Kit** (not pictured)	<b>VL0808DRW</b>
8"w x 24"d	Compartment Shelf	<b>VL0808</b>
-	Double Prong Hook	<b>NF6712</b>
Boot Tray Options		
10"w x 24"d	Boot Tray	<b>VL184BT</b>

### Step 2 Configuration A

Upper Unit Partition Kit consists of the following components (to configure locker using partition kit see personal compartment options below)		
24"w x 24"d	Partition Kit	<b>VL2458PT</b>
18"w	Full Width Shelf†	
-	Two Utility Hooks	
18"w	Coat Rod	
Upper Unit options AVAILABLE ONLY WITH a Partition Kit		
Personal Compartment Options		
8"w x 8"h	Security Compartment Door Kit**	<b>VL0808LU</b>
8"w x 8"h	Two Drawer/Shelf Kit** (not pictured)	<b>VL0808DRW</b>
8"w x 24"d	Compartment Shelf	<b>VL0808</b>
-	Double Prong Hook	<b>NF6712</b>
Boot Tray Options		
16"w x 24"d	Boot Tray	<b>VL244BT</b>

### Step 2 Configuration B

Upper Unit Options AVAILABLE ONLY WITHOUT a Partition Kit		
Upper Shelf Options		
18"w	Full Width Shelf†	<b>VL184SS</b>
18"w	Vest Shelf†	<b>VL184VS</b>
Stand Alone Security Compartment		
8"w x 12"d x 11"h	Stand Alone Security Comp.††	<b>VL081211</b>
12"w x 20.625"d x 11"h	Stand Alone Security Comp.††	<b>VL122411</b>

### Step 2 Configuration B

Upper Unit Options AVAILABLE ONLY WITHOUT a Partition Kit		
Upper Shelf Options		
24"w	Full Width Shelf†	<b>VL244SS</b>
24"w	Vest Shelf†	<b>VL244VS</b>
Stand Alone Security Compartment		
8"w x 12"d x 11"h	Stand Alone Security Comp.††	<b>VL081211</b>
12"w x 20.625"d x 11"h	Stand Alone Security Comp.††	<b>VL122411</b>

### Step 3 Lower Drawer Unit

18"w x 36"d x 18"h	Lower Drawer Unit	<b>VL1836DRW</b>
18"w x .75"h	18"w Hardwood Bench Top	<b>100760-18X.75</b>
18"w x 24"d	Vest Shelf for Lower Drawer Unit	<b>VL1821DV</b>

### Step 3 Lower Drawer Unit

24"w x 36"d x 18"h	Lower Drawer Unit	<b>VL2436DRW</b>
18"w x .75"h	24"w Hardwood Bench Top	<b>100760-24X.75</b>
24"w x 24"d	Vest Shelf for Lower Unit Drawer	<b>VL2421DV</b>

### Step 4

#### Accessories for BOTH 18" and 24" Base Lockers

Locker Door Options		
-	Clip Board Holder (not pictured)	<b>VL0808CB</b>
7"w x 11"h	Mirror with Magnetic Backing	<b>NFVLMIRROR</b>
-	Belt Clips, (3-pack)	<b>NFVLHOOK</b>

† Up to two additional shelves may be used above the partition kit.

\*\* A compartment shelf (No. VL0808) is necessary to close the tops of these items unless mounted directly below full shelf.

†† A stand alone security compartment may be secured above or below a full width shelf when a partition kit is not used. (Please review with Lyon sales representative when ordering to confirm correct configuration).